

Garant**CNC storage shelf, Width 1000 mm, for tool shanks: HSK80****Order data**

Order number	970660 HSK80
GTIN	4045197489166
Item class	91L

Description**Version:**

Sheet metal storage shelves with plastic GARANT tool sockets. Front face with square lip for stabilisation. **Range of depth adjustment 130 mm.** Stops available **horizontal 90°** and **inclined 120°**

Suitable for:

Assembly by **insertion** in **support columns (Group 92)**, **CNC racking No. 970680** and **material supply trolleys No. 918590 size 1000 (Group 91)**.

Colour:

Light grey RAL 7035, **powder-coated.**

Note:

Load capacity in support columns 25 kg;
Load capacity in CNC racks and material trolleys 50 kg.

Technical description

Number of tool sockets	7
Depth	155 mm
Axial spacing A	110 mm
Height	80 mm
Width	1000 mm
for tool shanks	HSK 80

Load capacity when inserted into support columns	25 kg
Load capacity in CNC racks and material trolleys	50 kg
Application range	CNC rack
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Width 1000 mm
Type of product	Storage shelf

Accessories

Plastic insert Type HSK80	947390 HSK80
---------------------------	--------------