

**Garant****CNC storage shelf, Width 1500 mm, for tool shanks: HSK63****Order data**

Order number	970665 HSK63
GTIN	4045197489289
Item class	91L

**Description****Version:**

Sheet metal storage shelves with plastic GARANT tool sockets. Front face with square lip for stabilisation. **Range of depth adjustment 130 mm.** Stops available **horizontal 90°** and **inclined 120°**

**Suitable for:**

Assembly by **insertion** in **support columns (Group 92)**, **CNC racking No. 970680** and **material supply trolleys No. 918590 size 1000 (Group 91)**.

**Colour:**

Light grey RAL 7035, **powder-coated.**

**Note:**

Load capacity in support columns 25 kg;  
Load capacity in CNC racks and material trolleys 50 kg.

**Technical description**

Depth	155 mm
Height	80 mm
Axial spacing A	85 mm
Number of tool sockets	15
Width	1500 mm
for tool shanks	HSK 63

Load capacity when inserted into support columns	25 kg
Load capacity in CNC racks and material trolleys	50 kg
Application range	CNC rack
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Width 1500 mm
Type of product	Storage shelf

---

## Accessories

Plastic insert Type HSK63	947390 HSK63
---------------------------	--------------