

AEG

Jigsaw, Type: STEP1200XE



Order data

Order number	078213 STEP1200XE
GTIN	4002395192762
Item class	07A

Description

Version:

Sturdy general-purpose jigsaws with metal gearbox casings and overload protection. With **FIXTEC quick-release clamping system** allows blades to be changed in seconds without any tools, and **selectable orbital stroke** for optimum cutting power and dust extraction combined with reduced saw blade wear.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Supplied with:

Supplied with chip break guard.

Supplied with 2 x saw blades, extraction adapter, sole plate, mains cable 4 m, carrying case.

Note:

Suitable spare batteries and chargers can be found under No. 073808 – 073840.

For jigsaw blades see No. 588400 – 588551.

Packaging: Carrying case

Manufacturer's designation: STEP1200XE

Power consumption: 730 W

Rate of strokes: 500 - 3000 min⁻¹

maximum sawn thickness steel: 10 mm

maximum sawn thickness wood: 135 mm

Mitre angle adjustment: yes

Technical description

maximum sawn thickness wood	135 mm
Orbital stroke	4-way
suitable jigsaw blades	588400 – 588551
maximum sawn thickness steel	10 mm
Weight	2.4 kg
Mitre angle adjustment	yes
Power consumption	730 W
maximum vibration to EN	10.5 m/s ²
Special features	general purpose use
Rate of strokes	500 - 3000 min ⁻¹
tool change without tools	yes, FIXTEC system
Manufacturer's designation	STEP1200XE
Packaging	Carrying case
Format	Straight handle
Power supply	Mains operated
Type of product	Saw

Accessories

Jigsaw blades set Designation T318A	588400 T318A
Jigsaw blades set Designation T118A	588400 T118A
Jigsaw blades set Designation T118AF	588400 T118AF
Jigsaw blades set Designation T118B	588400 T118B
Jigsaw blades set Designation T127D	588400 T127D
Jigsaw blades set Designation T318B	588400 T318B
Jigsaw blades set Designation T118AHM	588400 T118AHM