



Tool cabinet complete with drawers, 36×36 U, Usable height mm / model: 1050/B



Order data

Order number	970780 1050/B
GTIN	4045197563415
Item class	91H

Description

Version:

Cabinet can be centrally locked by a cylinder lock. With anti-roll lip on 3 sides, black (H = 25 mm) with **ribbed rubber covering**. **Fork lift / pallet truck base 100 mm** high.

Colour:

Body light grey RAL 7035, drawers mouse grey RAL 7005 **powder-coated**.

Note:

For storage of tools, a drawer inlay No. 970700 is required.

Drawer runner extension (partial/full extension): 100 %

Drawer runner extension: Anti-tilt lock

Height adjustment interval: 25 mm

Cylinder lock: modular barrel

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Safety certificate: GS TÜV Rheinland

Height: 1270 mm

Width: 717 mm

Depth: 725 mm

Usable height: 1050 mm

Height of anti-roll lip: 25 mm

Drawer usable width: 612 mm

Technical description

Type of base	Fork-lift truck base
Type of base	Pallet truck base
Depth	725 mm
Drawer usable depth	612 mm
Anti-roll lip version	on 3 sides
Height	1270 mm
Drawer usable width	612 mm
Usable height	1050 mm
Width	717 mm
Electronic locking system can be retrofitted	yes
Depth in units	36 E
Width in units	36 E
Height of anti-roll lip	25 mm
Number of drawers	5
Material thickness	1.2 mm
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Safety certificate	GS TÜV Rheinland
Width×depth in units	36×36 U

Accessories

914236

Lock plate for Group 94 workbench drawer units without
cylinder insert
