

Storage shelf, basic rack, Depth 800 mm, Height / Shelf width: 3000/750mm**Order data**

| | |
|--------------|-----------------|
| Order number | 990552 3000/750 |
| GTIN | 4004514237927 |
| Item class | 96P |

Description**Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 250 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|---|-----------------|
| Depth | 836 mm |
| Rack height | 3000 mm |
| Width | 810 mm |
| Rack installation | Basic rack |
| Height | 3000 mm |
| Number of shelves | 7 |
| Number of profile frames | 2 |
| Assembled size basic rack width | 810 mm |
| Storage shelf depth | 800 mm |
| Rack depth | 800 mm |
| Shelf width | 750 mm |
| maximum bay load | 1600 kg |
| Shelf load capacity / maximum distributed shelf load (on metal) | 250 kg |
| Shelf thickness | 40 mm |
| Height adjustment interval | 25 mm |
| Type of installation | Plug-in racking |
| Material | galvanized |
| Product name attribute | Depth 800 mm |
| Type of product | Storage shelf |