

Storage shelf, add-on rack, Depth 800 mm, Height / Shelf width: 2000/750mm



Order data

Order number	990554 2000/750
GTIN	4004514237934
Item class	96P

Description

Version:

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 250 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

Load per bay: for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

Description:

Assembled size:

Basic rack: Nominal length + 60 mm

Extension rack: Nominal length + +6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

Supplied with:

Basic rack with cross braces. One diagonal brace per extension rack.

Note:

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Width	756 mm
Rack height	2000 mm
Assembled size add-on rack width	756 mm
Number of profile frames	1
Depth	836 mm
Rack installation	Extension rack
Number of shelves	5
Height	2000 mm
Storage shelf depth	800 mm
Rack depth	800 mm
Shelf width	750 mm
maximum bay load	1300 kg
Shelf load capacity / maximum distributed shelf load (on metal)	250 kg
Shelf thickness	40 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanized
Product name attribute	Depth 800 mm
Type of product	Storage shelf