

**Pair of gloves Camapur® Cut 627+, Glove size: 8****Order data**

Order number	094476 8
GTIN	4008198862789
Item class	04Q

**Description****Version:**

**Camapur® Cut 627+.** Flexible gloves with cut protection for assembly work under dry and slightly oily working conditions. With a thin PU coating for high wearing comfort and increased breathability. Good security of grip, even on oily components. Particularly suitable for metal processing, assembly work with medium cut hazards.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

Glove size	8
Accuracy of fit	very good
EN 388 abrasion resistance	4
DMF-free	yes

Breathability	very good
Manufacturer's designation	Camapur Cut 627+
Touch sensitivity	good
Material of coating	PU
Wet grip	medium
EN 388 tear propagation resistance	4
EN 388 cut resistance	3
Oil grip	medium
Heat protection	not available
silicone-free	yes
Series	Camapur®
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	14
Knitted technology	13G
electrostatic characteristic	0.3 sec. in accordance with charge decay specifications in EN 61340-5-1
EN 388	4341X
Backing material	HPPE
Coating	PU
Coating variant	The palms of the hands
Application range	All-round
Colour	grey / black
Weight	73 g
Length	240 - 260 mm
Application	reusable
Cut protection class	B
Type of product	Cut-resistant gloves

