

**Storage shelf, basic rack, Depth 800 mm, Height / Shelf width: 2000/1300mm****Order data**

|              |                  |
|--------------|------------------|
| Order number | 990552 2000/1300 |
| GTIN         | 4004514217868    |
| Item class   | 96P              |

**Description****Version:**

T-profile frames and storage shelves galvanised. Available with a maximum **bay load capacity** of 250 kg per shelf. Storage shelf levels adjustable at 25 mm intervals. Quick assembly thanks to the simple plug-in design.

**Load per bay:** for height 2000 mm 1300 kg, for 2500 mm 1700 kg, for 3000 mm 2300 kg.

**Description:****Assembled size:**

**Basic rack:** Nominal length + 60 mm

**Extension rack:** Nominal length + +6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Application:**

Ideal for industry, craft, trade, administration, archives etc. with optimum use of space.

**Supplied with:**

Basic rack with cross braces. One diagonal brace per extension rack.

**Note:**

- **Clamp feet are supplied.**
- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Access from one side only due to use of diagonal braces.**
- **The free unsupported length (K) must not be more than 600 mm.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

|   |                 |
|---|-----------------|
| Number of shelves   | 5               |
| Assembled size basic rack width                                 | 1360 mm         |
| Rack height   | 2000 mm         |
| Rack installation   | Basic rack      |
| Number of profile frames  | 2               |
| Storage shelf depth   | 800 mm          |
| Rack depth  | 800 mm          |
| Shelf width   | 1300 mm         |
| maximum bay load  | 1300 kg         |
| Shelf load capacity / maximum distributed shelf load (on metal) | 250 kg          |
| Shelf thickness   | 40 mm           |
| Height adjustment interval                                      | 25 mm           |
| Type of installation  | Plug-in racking |
| Material  | galvanized      |
| Product name attribute  | Depth 800 mm    |
| Type of product   | Storage shelf   |

## Accessories

|   |                |
|---|----------------|
| Plug-in dividers, fixed, galvanized Height × depth 210X800 mm | 990583 210X800 |
| Plug-in dividers, fixed, galvanized Height × depth 310X800 mm | 990583 310X800 |
| Plug-in dividers, fixed, galvanized Height × depth 410X800 mm | 990583 410X800 |
| Clamping base   | 990852         |

