

Inclined shelf basic rack, Width 1000 mm, Depth: 800mm



Order data

Order number	990600 800
GTIN	4004514218803
Item class	96P

Description

Version:

T-profile frames and storage shelves galvanised. Available with a **maximum load capacity of 150 kg per inclined shelf**. Storage shelf levels adjustable at 25-mm intervals. Quick assembly thanks to the simple plug-in design. Can be accessed from both sides. **Load per bay: 1300 kg.**

Assembled size of basic rack: 1060 mm

Horizontal divider guides can be adjusted at 50 mm steps. The front lengthways bar is raised 15 mm and thus prevents goods falling off the shelves.

Description:

Assembled size:

Basic rack: Nominal length + 60mm

Extension rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Accepts plastic containers, clear-view containers, boxes and much more.

Supplied with:

7 inclined shelves each with 5 divider guides. 2 longitudinal bars. 2 lateral guides and 1 horizontal cover, including clip-on feet.

Note:

- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**

- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Assembled size basic rack width	1060 mm
Number of shelves	7
Depth	836 mm
Height	2000 mm
Customer assembly	yes
Width	1060 mm
Rack depth	800 mm
Rack width	1000 mm
Rack height	2000 mm
maximum bay load	1300 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Width 1000 mm
Type of product	Inclined shelf racking

Accessories

Inclined shelf, galvanised Depth 800 mm	990610 800
Clamping base	990852