

**Inclined shelf extension rack, Width 1000 mm, Depth: 500mm****Order data**

Order number	990602 500
GTIN	4004514249210
Item class	96P

**Description****Version:**

Inclined shelf/Kanban racking that can be accessed from both sides, ideal for First-in-First-Out storage as the stored goods can slip to the front on the smooth galvanised shelves.

T-profile frames and storage shelves galvanised. Available with a **maximum load capacity of 150 kg per inclined shelf**. Storage shelf levels adjustable at 25-mm intervals. Quick assembly thanks to the simple plug-in design. Can be accessed from both sides. **Load per bay: 1300 kg**. Horizontal divider guides can be adjusted at 50 mm steps. The front lengthways bar is raised 15 mm and thus prevents goods falling off the shelves.

Assembled size of extension rack: 1006 mm

**Description:****Assembled size:**

**Basic rack:** Nominal length + 60mm

**Extension rack:** Nominal length + 6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Application:**

Accepts plastic containers, clear-view containers, boxes and much more.

**Supplied with:**

7 inclined shelves each with 5 divider guides. 2 longitudinal bars. 2 lateral guides and 1 horizontal cover, including clip-on feet.

**Note:**

- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

### Technical description

Height	2000 mm
Assembled size add-on rack width	1006 mm
Customer assembly	yes
Depth	536 mm
Number of shelves	7
Width	1006 mm
Rack depth	500 mm
Rack width	1000 mm
Rack height	2000 mm
maximum bay load	1300 kg
Shelf load capacity / maximum distributed shelf load (on metal)	150 kg
Shelf thickness	25 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Width 1000 mm
Type of product	Inclined shelf racking

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/990602-500>