

Inclined shelf extension rack, Width 1000 mm, Depth: 800mm



Order data

| | |
|--------------|---------------|
| Order number | 990602 800 |
| GTIN | 4004514218810 |
| Item class | 96P |

Description

Version:

Inclined shelf/Kanban racking that can be accessed from both sides, ideal for First-in-First-Out storage as the stored goods can slip to the front on the smooth galvanised shelves.

T-profile frames and storage shelves galvanised. Available with a **maximum load capacity of 150 kg per inclined shelf**. Storage shelf levels adjustable at 25-mm intervals. Quick assembly thanks to the simple plug-in design. Can be accessed from both sides. **Load per bay: 1300 kg.**

Assembled size of extension rack: 1006 mm

Horizontal divider guides can be adjusted at 50 mm steps. The front lengthways bar is raised 15 mm and thus prevents goods falling off the shelves.

Description:

Assembled size:

Basic rack: Nominal length + 60mm

Extension rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 36 mm

Application:

Accepts plastic containers, clear-view containers, boxes and much more.

Supplied with:

7 inclined shelves each with 5 divider guides. 2 longitudinal bars. 2 lateral guides and 1 horizontal cover, including clip-on feet.

Note:

- **Floor and wall fastenings are not included.**
- **Suitable floor anchoring No. 990854.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|---|------------------------|
| Customer assembly | yes |
| Number of shelves | 7 |
| Depth | 836 mm |
| Assembled size add-on rack width | 1006 mm |
| Height | 2000 mm |
| Width | 1006 mm |
| Rack depth | 800 mm |
| Rack width | 1000 mm |
| Rack height | 2000 mm |
| maximum bay load | 1300 kg |
| Shelf load capacity / maximum distributed shelf load (on metal) | 150 kg |
| Shelf thickness | 25 mm |
| Height adjustment interval | 25 mm |
| Type of installation | Plug-in racking |
| Material | galvanised |
| Product name attribute | Width 1000 mm |
| Type of product | Inclined shelf racking |

Accessories

| | |
|---|------------|
| Inclined shelf, galvanised Depth 800 mm | 990610 800 |
| Clamping base | 990852 |