

uvex

Pair of gloves uvex C500 foam, Glove size: 9



Order data

Order number	094550 9
GTIN	4048612015124
Item class	04W

Description

Version:

uvex C500 foam. Silicone-free gloves with good mechanical abrasion resistance and very good grip in dry and slightly damp environments. For contact heat up to 100°C.

uvex 500 series. Reliable cut-resistant gloves with bamboo TwinFlex® technology of bamboo viscose, HPPE and polyamide for a pleasant wearing sensation and advanced climatic regulation.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

DMF-free	no
Wet grip	medium
EN 388 cut resistance	5
Accuracy of fit	very good
Glove size	9

Heat protection	not available
Touch sensitivity	very good
silicone-free	yes
EN 388 abrasion resistance	4
EN 388 penetration resistance	2
Oil grip	medium
Breathability	good
EN 388 tear propagation resistance	4
Series	uvex C500
Type of glove	Cut-resistant gloves
Protection category	Category II
Glove characteristics	Silicone-free
Clothing standard	Oeko-Tex Standard 100
EN 388	4X42C
EN 407	X1XXXX
Backing material	Polyamide, HPPE, glass, bamboo, viscose
Coating	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Colour	anthracite / lime
Standard	EN 407
Weight	32.8 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves