

**HOLEX****Fleece velour-backed abrasive disc, Ø 125 mm, Grit equivalent: 180****Order data**

Order number	GG5695 180
GTIN	4045197575203
Item class	GGN

**Description****Version:**

Fleece velour-backed abrasive discs with through-stitched backing for hook and loop fastening. With removable centre for more precise positioning and attachment of the disc to the backing pad (**approx. 50 % reduction in vibration level with velour-backed abrasive discs No. 566965**).

Corresponds to 566950.

**Version of the advertising text:**

Fleece velour-backed abrasive disc with removable centre (**same as 566940; 566950**).

**Application:**

On angle grinders with hook and loop fastener backing pad No. 566960 or 566965.

For **finishing, matting, smoothing** with significant reduction in roughness, and for **light cleaning** (such as removal of discolouration) and **deburring tasks**.

**Content:**

80 discs / drum.

**Note:**

See No. **567705ff** onwards for velour-backed abrasive discs for rough abrasion.

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.**

**Technical description**

Version	A medium
Grit equivalent	180
Disc Ø	125 mm
Colour	red
Grit designation	medium
Contents	80
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
maximum circumferential speed	40 m/s
Type of product	Non-woven abrasive

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		

wet maximum	suitable only under restricted conditions
dry	suitable

---

## Accessories

Fleece velour-backed abrasive disc Grit equivalent 180	566950 180
--	------------