

**Fibre disc Aluminium Oxide (A), Ø 115 mm, Grit: 40****Order data**

Order number	GG5641 40
GTIN	4045197296023
Item class	GGN

Description**Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. **HOLEX universal fibre disc** for grinding all metals. Grit type: **Aluminium oxide (A)**, same as 566410.

Version of the advertising text:

General-purpose fibre discs with tear-resistant, very pliable vulcanised fibre. Bore Ø 22.23 mm with cross slits. Grit type: Regular aluminium oxide (A) (**same as 566410, 566510, 566610**). For grinding all metals, wood and plastics.

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Content:

250 pieces / bulk pack.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Grit	40
Disc Ø	115 mm
Contents	250

Grinding media	Regular aluminium oxide (A)
Grinding medium code	A
Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Adapter	Roloc™ quick-change system
Bore Ø	22.23 mm
suitable for quick-change system	Roloc™
optimised for material	Steel
maximum circumferential speed	80 m/s
maximum speed	13300 min ⁻¹

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

Accessories

Fibre disc Aluminium Oxide(A) Grit 40

566410 40