

**HOLEX**
**Fibre disc Aluminium Oxide (A), Ø 115 mm, Grit: 60**

**Order data**

Order number	GG5641 60
GTIN	4045197296030
Item class	GGN

**Description**
**Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. **HOLEX universal fibre disc** for grinding all metals. Grit type: **Aluminium oxide (A)**, same as 566410.

**Version of the advertising text:**

General-purpose fibre discs with tear-resistant, very pliable vulcanised fibre. Bore Ø 22.23 mm with cross slits. Grit type: Regular aluminium oxide (A) (**same as 566410, 566510, 566610**). For grinding all metals, wood and plastics.

**Application:**

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

**Content:**

250 pieces / bulk pack.

**Note:**

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.**

**Technical description**

Grit	60
Disc Ø	115 mm
Contents	250

Grinding media	Regular aluminium oxide (A)
Grinding medium code	A
Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Adapter	Roloc™ quick-change system
Bore Ø	22.23 mm
suitable for quick-change system	Roloc™
optimised for material	Steel
maximum circumferential speed	80 m/s
maximum speed	13300 min <sup>-1</sup>

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

## Accessories

Fibre disc Aluminium Oxide(A) Grit 60

566410 60