

uvex**Pair of gloves uvex C500 foam, Glove size: 10**

Order data

| | |
|--------------|---------------|
| Order number | 094550 10 |
| GTIN | 4048612015131 |
| Item class | 04W |

Description

Version:

uvex C500 foam. Silicone-free gloves with good mechanical abrasion resistance and very good grip in dry and slightly damp environments. For contact heat up to 100°C.

uvex 500 series. Reliable cut-resistant gloves with bamboo TwinFlex® technology of bamboo viscose, HPPE and polyamide for a pleasant wearing sensation and advanced climatic regulation.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|-------------------------------|---------------|
| EN 388 penetration resistance | 2 |
| DMF-free | no |
| Heat protection | not available |
| Accuracy of fit | very good |
| Oil grip | medium |

| | |
|------------------------------------|--|
| Wet grip | medium |
| EN 388 tear propagation resistance | 4 |
| Touch sensitivity | very good |
| EN 388 abrasion resistance | 4 |
| silicone-free | yes |
| Breathability | good |
| EN 388 cut resistance | 5 |
| Glove size | 10 |
| Series | uvex C500 |
| Protection category | Category II |
| Type of glove | Cut-resistant gloves |
| Glove characteristics | Silicone-free |
| Clothing standard | Oeko-Tex Standard 100 |
| EN 388 | 4X42C |
| EN 407 | X1XXXX |
| Backing material | Polyamide, HPPE, glass, bamboo, viscose |
| Coating | Nitrile |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Colour | anthracite / lime |
| Standard | EN 407 |
| Weight | 32.8 g |
| Application | reusable |
| Cut protection class | C |
| Type of product | Cut-resistant gloves |