

**Pair of gloves 6705, Glove size: 11****Order data**

Order number	094530 11
GTIN	4059904096677
Item class	09H

Description**Version:**

6705. PU coating for high breathability and freedom of movement for working in damp but not oily environments.

Version of the advertising text:

Cut-resistant gloves (class 5) with **outstanding cost-benefit ratio**.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Material of coating	PU
Breathability	good
silicone-free	yes
EN 388 cut resistance	5

Wet grip	medium
Glove size	11
DMF-free	no
Oil grip	medium
EN 388 abrasion resistance	4
Accuracy of fit	good
EN 388 tear propagation resistance	4
Touch sensitivity	good
EN 388 penetration resistance	2
Heat protection	good
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	10
Knitted technology	13G
EN 388	4442C
EN 407	X1XXXX
Backing material	Taeki
Coating	PU
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Standard	EN 407
Weight	31.8 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves