

Wide-span add-on rack, Depth 600 mm, Height / Shelf width: 3000/1500mm**Order data**

Order number	990725 3000/1500
GTIN	4004514215314
Item class	96P

Description**Version:**

Galvanised T-profile frames. With MULTI^{plus} 250 galvanised sheet metal storage shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf:** 400 kg. **Load per bay:** for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 36 mm

Height of the cross beams: 65 mm

Application:

Storage of awkward and bulky goods. Access from both sides allows for short picking distances.

Note:

- **The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.**
- **Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.**
- **Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**

- **The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Height	3000 mm
Storage shelf depth	600 mm
Shelf width	1500 mm
Assembled size add-on rack width	1506 mm
Material of storage level	Galvanised sheet metal
Width	1506 mm
Customer assembly	yes
Rack installation	Extension rack
Number of storage levels	5
Depth	637 mm
Rack depth	600 mm
Rack width	1500 mm
Rack height	3000 mm
Shelf load capacity	400 kg
maximum bay load	1800 kg
Shelf load capacity / maximum distributed shelf load (on metal)	400 kg
Shelf thickness	40 mm
Cross beam height	65 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 600 mm
Type of product	Wide-span racking

Accessories

Sheet metal storage shelf galvanised Depth 600 mm	990790 600
Clamping base	990852