

## Wide-span add-on rack, Depth 400 mm, Height / Shelf width: 2500/2500mm



### Order data

|              |                  |
|--------------|------------------|
| Order number | 990705 2500/2500 |
| GTIN         | 4004514200921    |
| Item class   | 96P              |

### Description

#### Version:

Galvanised T-profile frames. With MULTI<sup>plus</sup> 250 galvanised sheet metal storage shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf**: 400 kg. **Load per bay**: for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

#### Description:

#### Assembled size:

**Basic rack:** Nominal length + 60 mm

**Add-on rack:** Nominal length + 6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Height of the cross beams:** 65 mm

#### Application:

Storage of awkward and bulky goods. Access from both sides allows for short picking distances.

#### Note:

- **The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.**
- **Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.**
- **Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**

- **The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

|   |                        |
|---|------------------------|
| Material of storage level                                       | Galvanised sheet metal |
| Shelf width   | 2500 mm                |
| Assembled size add-on rack width                                | 2506 mm                |
| Storage shelf depth   | 400 mm                 |
| Number of storage levels  | 4                      |
| Width   | 2506 mm                |
| Height  | 2500 mm                |
| Rack installation   | Extension rack         |
| Customer assembly   | yes                    |
| Depth   | 437 mm                 |
| Rack depth  | 400 mm                 |
| Rack width  | 2500 mm                |
| Rack height   | 2500 mm                |
| Shelf load capacity   | 400 kg                 |
| maximum bay load  | 1600 kg                |
| Shelf load capacity / maximum distributed shelf load (on metal) | 400 kg                 |
| Shelf thickness   | 40 mm                  |
| Cross beam height   | 65 mm                  |
| Height adjustment interval                                      | 25 mm                  |
| Type of installation  | Plug-in racking        |
| Material  | galvanised             |
| Product name attribute  | Depth 400 mm           |
| Type of product   | Wide-span racking      |

---

**Accessories**

|   |            |
|---|------------|
| Sheet metal storage shelf galvanised Depth 400 mm | 990805 400 |
| Clamping base                                     | 990852     |