

**Wide-span add-on rack, Depth 500 mm, Height / Shelf width: 3000/2250mm****Order data**

Order number	990715 3000/2250
GTIN	4004514215383
Item class	96P

**Description****Version:**

Galvanised T-profile frames. With MULTI<sup>plus</sup> 250 galvanised sheet metal storage shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf:** 400 kg. **Load per bay:** for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

**Description:****Assembled size:**

**Basic rack:** Nominal length + 60 mm

**Add-on rack:** Nominal length + 6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Height of the cross beams:** 65 mm

**Application:**

Storage of awkward and bulky goods. Access from both sides allows for short picking distances.

**Note:**

- **The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.**
- **Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.**
- **Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**

- **The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Number of storage levels	5
Rack installation	Extension rack
Material of storage level	Galvanised sheet metal
Height	3000 mm
Width	2256 mm
Customer assembly	yes
Assembled size add-on rack width	2256 mm
Storage shelf depth	500 mm
Shelf width	2250 mm
Depth	537 mm
Rack depth	500 mm
Rack width	2250 mm
Rack height	3000 mm
Shelf load capacity	400 kg
maximum bay load	1800 kg
Shelf load capacity / maximum distributed shelf load (on metal)	400 kg
Shelf thickness	40 mm
Cross beam height	65 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 500 mm
Type of product	Wide-span racking

---

**Accessories**

Sheet metal storage shelf galvanised Depth 500 mm	990800 500
Clamping base	990852