

## Wide-span basic rack, Depth 400 mm, Height / Shelf width: 2500/2000mm



### Order data

Order number	990700 2500/2000
GTIN	4004514215031
Item class	96P

### Description

#### Version:

Galvanised T-profile frames. With MULTI<sup>plus</sup> 250 galvanised sheet metal storage shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf**: 400 kg. **Load per bay**: for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

#### Description:

#### Assembled size:

**Basic rack:** Nominal length + 60 mm

**Add-on rack:** Nominal length + 6 mm

**Overall depth of the rack:** Nominal depth + 36 mm

**Height of the cross beams:** 65 mm

#### Application:

Storage of awkward and bulky goods. Access from both sides allows for short picking distances.

#### Note:

- **The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.**
- **Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.**
- **Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**

- **The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

## Technical description

Storage shelf depth	400 mm
Customer assembly	yes
Rack installation	Basic rack
Height	2500 mm
Shelf width	2000 mm
Number of storage levels	4
Material of storage level	Galvanised sheet metal
Width	2060 mm
Assembled size basic rack width	2060 mm
Depth	437 mm
Rack depth	400 mm
Rack width	2000 mm
Rack height	2500 mm
Shelf load capacity	400 kg
maximum bay load	1600 kg
Shelf load capacity / maximum distributed shelf load (on metal)	400 kg
Shelf thickness	40 mm
Cross beam height	65 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 400 mm
Type of product	Wide-span racking

---

**Accessories**

Sheet metal storage shelf galvanised Depth 400 mm	990795 400
Clamping base	990852