

**Pair of gloves Waredex Work® 550, Glove size: 11****Order data**

Order number	094545 11
GTIN	4008198755012
Item class	04Q

Description**Version:**

Waredex Work® 500. Roughened coating of polyurethane for a good grip for dealing with oily or wet objects. Good fit and touch sensitivity, ensuring a high comfort for the wearer. Very high cut resistance in combination with mechanical barrier.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

EN 388 tear propagation resistance	4
EN 388 abrasion resistance	4
Glove size	11
DMF-free	yes
Heat protection	not available

Oil grip	medium
Breathability	very good
Material of coating	PU
Accuracy of fit	very good
Touch sensitivity	good
EN 388 cut resistance	5
Manufacturer's designation	Waredex Work 550
silicone-free	yes
Wet grip	medium
Protection category	Category II
Type of glove	Cut-resistant gloves
Contents	16
Glove characteristics	Foodstuffs certified
Knitted technology	13G
electrostatic characteristic	0.2 sec. in accordance with charge decay specifications in EN 61340-5-1
EN 388	4541X
Backing material	HPPE, glass
Coating	PU
Coating variant	The palms of the hands
Application range	All-round
Colour	grey / beige
Weight	75 g
Length	255 - 265 mm
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves

