

uvex**Pair of gloves uvex C300 foam, Glove size: 9**

Order data

| | |
|--------------|---------------|
| Order number | 094480 9 |
| GTIN | 4048612021835 |
| Item class | 04W |

Description

Version:

uvex 300 series. Lightweight innovative gloves with bamboo TwinFlex® technology offers good cut protection, high abrasion resistance and pleasant sensation when wearing. The climazone process ensures high flexibility and good temperature regulation, whilst also offering a good sense of touch. To Öko-Tex® standard 100 and free of silicone.

uvex C300 foam. With Soft-Grip-Foam coating for a secure grip in wet working conditions.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|-------------------------------|--------|
| silicone-free | yes |
| EN 388 penetration resistance | 2 |
| Oil grip | medium |
| Material of coating | PU |

| | |
|------------------------------------|--|
| EN 388 tear propagation resistance | 4 |
| Breathability | good |
| Touch sensitivity | very good |
| DMF-free | yes |
| Heat protection | not available |
| Wet grip | medium |
| Glove size | 9 |
| Accuracy of fit | very good |
| EN 388 cut resistance | 3 |
| EN 388 abrasion resistance | 4 |
| Series | uvex C300 |
| Protection category | Category II |
| Type of glove | Multi-purpose gloves |
| Glove characteristics | Silicone-free |
| Clothing standard | Oeko-Tex Standard 100 |
| EN 388 | 3X42C |
| Backing material | Polyamide, HPPE, glass, bamboo, viscose |
| Coating | Nitrile |
| Coating variant | The palms of the hands |
| Application range | All-round |
| Colour | black |
| Weight | 14.9 g |
| Application | reusable |
| Cut protection class | C |
| Type of product | Cut-resistant gloves |