

Ansell**Pair of gloves HyFlex® 11-518, Glove size: 7****Order data**

| | |
|--------------|----------------|
| Order number | 094478 7 |
| GTIN | 10076490478626 |
| Item class | 04P |

Description**Version:**

HyFlex® 11-518. Fine and flexible gloves with **light weight** of only 14 gm. Together with **high freedom of movement for the fingers** for less tiredness of the hand muscles when used for long periods. With **18 gauge knitted fabric** and Dyneema® diamond technology fibres. Particularly suitable for handling and assembly of extremely small sharp-edged components.

Version of the advertising text:

PU-coated cut-resistant gloves with **high dexterity**, optimum for working with sharp-edged components.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

| | |
|----------------------------|------|
| Oil grip | good |
| DMF-free | no |
| EN 388 abrasion resistance | 3 |

| | |
|------------------------------------|--------------------------------|
| Accuracy of fit | very good |
| Material of coating | PU |
| Touch sensitivity | very good |
| Breathability | good |
| EN 388 tear propagation resistance | 3 |
| Wet grip | good |
| Heat protection | not available |
| Glove size | 7 |
| silicone-free | no |
| EN 388 cut resistance | 3 |
| Series | HyFlex® |
| Protection category | Category II |
| Type of glove | Multi-purpose gloves |
| Contents | 12 |
| Glove characteristics | Suitable for allergy sufferers |
| Knitted technology | 18G |
| EN 388 | 3X31B |
| Backing material | Nylon; Dyneema® |
| Coating | PU |
| Material | PU |
| Coating variant | The palms of the hands |
| Application range | Precision |
| Colour | blue |
| Weight | 14 g |
| Length | 210 mm |
| Application | reusable |
| Cut protection class | B |
| Type of product | Cut-resistant gloves |

