

Wide-span basic rack, Depth 800 mm, Height / Shelf width: 3000/2000mm**Order data**

| | |
|--------------|------------------|
| Order number | 990730 3000/2000 |
| GTIN | 4004514215215 |
| Item class | 96P |

Description**Version:**

Galvanised T-profile frames. With MULTI^{plus} 250 galvanised sheet metal storage shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf:** 400 kg. **Load per bay:** for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 36 mm

Height of the cross beams: 65 mm

Application:

Storage of awkward and bulky goods. Access from both sides allows for short picking distances.

Note:

- **The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.**
- **Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.**
- **Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**

- **The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|---|------------------------|
| Width | 2060 mm |
| Rack installation | Basic rack |
| Material of storage level | Galvanised sheet metal |
| Assembled size basic rack width | 2060 mm |
| Number of storage levels | 5 |
| Height | 3000 mm |
| Shelf width | 2000 mm |
| Customer assembly | yes |
| Storage shelf depth | 800 mm |
| Depth | 837 mm |
| Rack depth | 800 mm |
| Rack width | 2000 mm |
| Rack height | 3000 mm |
| Shelf load capacity | 400 kg |
| maximum bay load | 1800 kg |
| Shelf load capacity / maximum distributed shelf load (on metal) | 400 kg |
| Shelf thickness | 40 mm |
| Cross beam height | 65 mm |
| Height adjustment interval | 25 mm |
| Type of installation | Plug-in racking |
| Material | galvanised |
| Product name attribute | Depth 800 mm |
| Type of product | Wide-span racking |

Accessories

| | |
|---|------------|
| Sheet metal storage shelf galvanised Depth 800 mm | 990795 800 |
| Clamping base | 990852 |