

uvex**Pair of gloves uvex C300 foam, Glove size: 10**

Order data

Order number	094480 10
GTIN	4048612021842
Item class	04W

Description

Version:

uvex 300 series. Lightweight innovative gloves with bamboo TwinFlex® technology offers good cut protection, high abrasion resistance and pleasant sensation when wearing. The climazone process ensures high flexibility and good temperature regulation, whilst also offering a good sense of touch. To Öko-Tex® standard 100 and free of silicone.

uvex C300 foam. With Soft-Grip-Foam coating for a secure grip in wet working conditions.

Standard:

EN 388; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Heat protection	not available
silicone-free	yes
EN 388 tear propagation resistance	4
Material of coating	PU

Wet grip	medium
EN 388 penetration resistance	2
EN 388 cut resistance	3
Oil grip	medium
EN 388 abrasion resistance	4
Glove size	10
Breathability	good
DMF-free	yes
Touch sensitivity	very good
Accuracy of fit	very good
Series	uvex C300
Type of glove	Multi-purpose gloves
Protection category	Category II
Glove characteristics	Silicone-free
Clothing standard	Oeko-Tex Standard 100
EN 388	3X42C
Backing material	Polyamide, HPPE, glass, bamboo, viscose
Coating	Nitrile
Coating variant	The palms of the hands
Application range	All-round
Colour	black
Weight	14.9 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves