

Wide-span add-on rack, Depth 800 mm, Height / Shelf width: 2000/2500mm**Order data**

Order number	990735 2000/2500
GTIN	4004514200310
Item class	96P

Description**Version:**

Galvanised T-profile frames. With MULTI^{plus} 250 galvanised sheet metal storage shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf:** 400 kg. **Load per bay:** for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

Description:**Assembled size:**

Basic rack: Nominal length + 60 mm

Add-on rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 36 mm

Height of the cross beams: 65 mm

Application:

Storage of awkward and bulky goods. Access from both sides allows for short picking distances.

Note:

- **The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.**
- **Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.**
- **Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.**

- **The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Shelf width	2500 mm
Height	2000 mm
Assembled size add-on rack width	2506 mm
Number of storage levels	3
Width	2506 mm
Material of storage level	Galvanised sheet metal
Storage shelf depth	800 mm
Rack installation	Extension rack
Customer assembly	yes
Depth	837 mm
Rack depth	800 mm
Rack width	2500 mm
Rack height	2000 mm
Shelf load capacity	400 kg
maximum bay load	1200 kg
Shelf load capacity / maximum distributed shelf load (on metal)	400 kg
Shelf thickness	40 mm
Cross beam height	65 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 800 mm
Type of product	Wide-span racking

Accessories

Sheet metal storage shelf galvanised Depth 800 mm	990805 800
Clamping base	990852