

## Wide-span basic rack, Depth 500 mm, Height / Shelf width: 3000/1500mm



### Order data

Order number	990750 3000/1500
GTIN	4004514215451
Item class	96P

### Description

#### Version:

Galvanised T-profile frames. With 19 mm chipboard shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf**: 400 kg. **Load per bay**: for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

#### Description:

#### Assembled size:

**basic rack:** Nominal length + 60 mm

**Extension rack:** Nominal length + 6 mm

**Overall depth of the rack:** Nominal depth + 37 mm

**Height of the cross beams:** 65 mm

#### Note:

- The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.
- Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.
- Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.
- The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.
- Supplied for self-assembly, saving freight costs. Delivered unassembled.

## Technical description

Width	1560 mm
Height	3000 mm
Number of storage levels	5
Assembled size basic rack width	1560 mm
Storage shelf depth	500 mm
Shelf width	1500 mm
Rack installation	Basic rack
Material of storage level	Chipboard shelf
Customer assembly	yes
Depth	537 mm
Rack depth	500 mm
Rack width	1500 mm
Rack height	3000 mm
Shelf load capacity	400 kg
maximum bay load	1800 kg
Workbench/desk load capacity - maximum distributed load (on wood)	400 kg
Insert thickness	19 mm
Cross beam height	65 mm
Height adjustment interval	25 mm
Type of installation	Plug-in racking
Material	galvanised
Product name attribute	Depth 500 mm
Type of product	Wide-span racking

## Accessories

Chipboard shelf storage level Depth 500 mm

990810 500