



Circulation filter attachment for safety cabinets



Order data

Order number	981100
GTIN	4250101104541
Item class	96G

Description

Version:

Complete system with exhaust air motor, special activated carbon filter, exhaust air flow, and filter monitoring. Casing of sheet metal.

Advantage:

- **No cost-intensive exhaust air ducting required.**
- **Easy and safe installation.**
- **Explosion hazard controls around the cabinet not required.**
- **High flexibility in the choice of equipment position.**
- **Active personnel protection due to reliable collection of vapours hazardous to health and their retention in the system filter. Filter saturation > 99.999 %.**
- **Whisper-quiet, only approx. 39 dB (A).**

Application:

For reliable technical ventilation of fume cabinets in working areas in accordance with the requirements of TRGS 510 Appendix 3.

Filter is suitable only for solvent vapours (hydrocarbons), not for corrosive aggressive substances such as citric acid.

Suitable for :

Safety cabinets No. 981015; 981025; 981035.

Colour:

Casing **powder-coated.**

Note:

- **A filter change with disposal of the contaminated filter by an asecos service engineer (at normal toxicity levels) is recommended once a year.**

Height: 210 mm
Width: 305 mm
Depth: 555 mm

Technical description

Height	210 mm
Depth	555 mm
Width	305 mm
Plug type, input	F
Nominal voltage	250 V
Type of product	Air circulation filter attachment