



Safety cabinet S-Classic type 90, Width: 1200mm



Order data

Order number	981025 1200
GTIN	2050001771957
Item class	96G

Description

Version:

Cabinet casing of sheet metal with integral door position detector, interior with chemically resistant surface.

- **Mountings for shelves at 32 mm intervals.**
- **Floor-level containment tray (satisfies StawaR).**
- **With exhaust air connection (NB 75).**
- **Including door position detector.**
- **Lockable with profile half-cylinder, can be integrated into the company's locking system. Not compatible with the Hoffmann locking system.**
- **With 4 height adjustment feet to compensate for unevenness in the floor.**

2-door

Application:

Secure storage in accordance with regulations of flammable hazardous substances in work areas.

Standard:

DIN EN 14470-1, Typgeprüft (Brandkammergetestet), **90 Minuten feuerbeständig (nach höchster Brandschutzstufe der TRGS 510 Anlage 3).**

Supplied with:

Cabinet with 3 storage shelves, perforated panel insert, and floor-level drip tray, plastic-coated, plus service log book.

Colour:

Cabinet housing and doors optionally RAL7035 pale grey **or** RAL1004 safety yellow **powder-coated**.

Note:

At regular intervals (annually), safety cabinets should be maintained and their operating characteristics checked by an authorised competent person.

Technical description

Width	1196 mm
Usable height	1742 mm
Number of floor-level containment trays	1
Number of shelves	3
Height	1968 mm
Number of perforated plate inserts	1
Usable width	1050 mm
Weight	453 kg
Usable depth	524 mm
Load capacity of shelf	75 kg
Volume of floor-level drip tray	33 l
Depth	616 mm
Height adjustment interval	32 mm
Fire resistance	90 min
Type of product	Safety cabinet