

**Pair of gloves 6705, Glove size: 7****Order data**

Order number	094530 7
GTIN	4059904096592
Item class	09H

**Description****Version:**

6705. PU coating for high breathability and freedom of movement for working in damp but not oily environments.

**Version of the advertising text:**

Cut-resistant gloves (class 5) with **outstanding cost-benefit ratio**.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

EN 388 tear propagation resistance	4
Wet grip	medium
EN 388 cut resistance	5
Oil grip	medium

DMF-free	no
Breathability	good
Glove size	7
EN 388 abrasion resistance	4
Heat protection	good
silicone-free	yes
Material of coating	PU
Touch sensitivity	good
EN 388 penetration resistance	2
Accuracy of fit	good
Protection category	Category II
Type of glove	Multi-purpose gloves
Contents	10
Knitted technology	13G
EN 388	4442C
EN 407	X1XXXX
Backing material	Taeki
Coating	PU
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Standard	EN 407
Weight	31.8 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves