



Stackable transport box with fixed sides, Nominal size depth×width: 800X500 mm



Order data

Order number	963521 800X500
GTIN	4052939502526
Item class	96l

Description

Version:

Made of sheet metal. High load capacity due to pressed steel sides with corner inserts.
Reinforced feet.
Sturdy stacking and attachment brackets with lifting eyes. Access height 105 mm.
Solid sides.

Colour:

Reseda green RAL 6011.
Height: 670 mm
Width: 550 mm
Depth: 850 mm
Capacity: 500 mm
Drive-in width: 600 mm
Drive-in depth: 410 mm

Technical description

can be lifted by crane	yes
stackable	no

Wall version	solid side
mixed stacking of different sizes is possible.	no
Depth	850 mm
Drive-in width	600 mm
Safe working load	800 kg
with fork insertion slots	no
Height	670 mm
Capacity	500 mm
Width	550 mm
Colour	reseda green RAL 6011
Material	Sheet steel
Stackable load	4000 kg
Pass-under height	105 mm
Weight	32 kg
Stacking edge on 3 sides	no
Attachment brackets with lifting eyes	yes
Drive-in depth	410 mm
Nominal width	500 mm
Nominal depth	800 mm
Manufacturer's designation	Transport and stacking container E
Type of product	Transport and stacking large container