

Wide-span basic rack, Depth 800 mm, Height / Shelf width: 3000/2000mm**Order data**

| | |
|--------------|------------------|
| Order number | 990770 3000/2000 |
| GTIN | 4004514215512 |
| Item class | 96P |

Description**Version:**

Galvanised T-profile frames. With 19 mm chipboard shelves. Storage shelf levels adjustable at 25 mm intervals. Simple plug-in cross pieces ensure quick assembly. Maximum **load per shelf:** 400 kg. **Load per bay:** for height 2000 mm 1200 kg, for 2500 mm 1600 kg, for 3000 mm 2000 kg.

Description:**Assembled size:**

basic rack: Nominal length + 60 mm

Extension rack: Nominal length + 6 mm

Overall depth of the rack: Nominal depth + 37 mm

Height of the cross beams: 65 mm

Note:

- The storage shelves are inserted in segments to suit the compartment width. Segments: 750 mm and 1000 mm.
- Floor and wall fastenings are not included. Suitable floor anchoring No. 990854.
- Wide-span racking WS 2000 is compatible with storage shelf racking No. 990500 – 990554, to which other dimensions and components also relate. We will be happy to quote you further options. If you are interested, please contact us.
- The free unsupported length (K) must not be more than 600 mm. The permissible bay load must be reduced by the amount of this shelf.
- Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

| | |
|---|-------------------|
| Assembled size basic rack width | 2060 mm |
| Rack installation | Basic rack |
| Customer assembly | yes |
| Storage shelf depth | 800 mm |
| Number of storage levels | 5 |
| Height | 3000 mm |
| Shelf width | 2000 mm |
| Material of storage level | Chipboard shelf |
| Width | 2060 mm |
| Depth | 837 mm |
| Rack depth | 800 mm |
| Rack width | 2000 mm |
| Rack height | 3000 mm |
| Shelf load capacity | 400 kg |
| maximum bay load | 1800 kg |
| Workbench/desk load capacity - maximum distributed load (on wood) | 400 kg |
| Insert thickness | 19 mm |
| Cross beam height | 65 mm |
| Height adjustment interval | 25 mm |
| Type of installation | Plug-in racking |
| Material | galvanised |
| Product name attribute | Depth 800 mm |
| Type of product | Wide-span racking |

Accessories

Chipboard shelf storage level Depth 800 mm

990815 800