



Stackable transport box with drop-down side, Nominal size depth×width: 800X500 mm



Order data

Order number	963523 800X500
GTIN	4052941124501
Item class	96l

Description

Version:

Made of sheet metal. High load capacity due to pressed steel sides with corner inserts.
Reinforced feet.
Sturdy stacking and attachment brackets with lifting eyes. Access height 105 mm.
With drop-down side.

Colour:

Reseda green RAL 6011.
Height: 670 mm
Width: 550 mm
Depth: 850 mm
Capacity: 500 mm
Drive-in width: 600 mm
Drive-in depth: 410 mm

Technical description

Drive-in depth	410 mm
mixed stacking of different sizes is possible.	no

Width	550 mm
Safe working load	800 kg
Capacity	500 mm
stackable	no
Pass-under height	105 mm
Material	Sheet steel
Height	670 mm
Stackable load	3200 kg
Drive-in width	600 mm
Weight	32 kg
with fork insertion slots	no
Stacking edge on 3 sides	no
Attachment brackets with lifting eyes	yes
Colour	reseda green RAL 6011
can be lifted by crane	yes
Depth	850 mm
Wall version	with drop-down side
Nominal width	500 mm
Nominal depth	800 mm
Manufacturer's designation	Transport and stacking container E
Type of product	Transport and stacking large container