



Pair of cut-resistant heat resistant gloves TAEKI 6750, Glove size: 10



Order data

Order number	094610 10
GTIN	4059904104907
Item class	09H

Description

Version:

TAEKI 6750. Uncoated **cut-resistant heat protection gloves** with reinforcement at the thumb joint. **Contact heat protection up to approx. 250°C** (maximum 15 seconds) with special knitted yarn. Heavy-duty version with **good touch sensitivity**.

Standard:

EN 388; EN 407; EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Cold protection	not available
Heat protection	very good
EN 388 abrasion resistance	4
Elasticated band	no
silicone-free	yes

DMF-free	yes
EN 388 cut resistance	5
Accuracy of fit	good
EN 388 penetration resistance	2
Breathability	very good
Oil grip	not available
EN 388 tear propagation resistance	4
Touch sensitivity	medium
EN 407 B: Contact heat (contact temperature at limit value time > 15 s)	250 °C
Glove size	10
Wet grip	not available
Type of glove	Heat protection gloves
Protection category	Category III
Glove characteristics	Flame resistance stage X
Glove characteristics	Silicone-free
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	DMF-free
EN 388	3X42C
EN 407	X2XXXX
Contact heat up to	250 °C
Backing material	Taeki
Coating variant	No coating
Colour	yellow
Application	reusable
Contents	10
Application range	All-round
Heat protection up to	250 °C
CE	2541
Standard	EN 407

Weight	43.8 g
Type of product	Heat protection gloves