



Stackable transport box with drop-down side, Nominal size depth×width: 1000X800 mm



Order data

Order number	963523 1000X800
GTIN	4052939501369
Item class	96l

Description

Version:

Made of sheet metal. High load capacity due to pressed steel sides with corner inserts.
Reinforced feet.
Sturdy stacking and attachment brackets with lifting eyes. Access height 105 mm.
With drop-down side.

Colour:

Reseda green RAL 6011.
Height: 670 mm
Width: 850 mm
Depth: 1050 mm
Capacity: 500 mm
Drive-in width: 800 mm
Drive-in depth: 700 mm

Technical description

Stackable load	7500 kg
with fork insertion slots	no

Weight	60 kg
Width	850 mm
Material	Sheet steel
Wall version	with drop-down side
Pass-under height	105 mm
Capacity	500 mm
Depth	1050 mm
Stacking edge on 3 sides	no
Colour	reseda green RAL 6011
Safe working load	1500 kg
Attachment brackets with lifting eyes	yes
mixed stacking of different sizes is possible.	no
stackable	no
can be lifted by crane	yes
Height	670 mm
Drive-in depth	700 mm
Drive-in width	800 mm
Nominal width	800 mm
Nominal depth	1000 mm
Manufacturer's designation	Transport and stacking container E
Type of product	Transport and stacking large container