



Stackable box with removal opening, Nominal size depth×width: 700X800 mm



Order data

Order number	963529 700X800
GTIN	4052941130021
Item class	96l

Description

Version:

Made of sheet metal. High load capacity due to pressed steel sides with corner inserts. Reinforced feet. Stacking edge round three sides (stackable up to 6 units). Access height 100 mm. Stacking edge round three sides (stackable up to 6 units). Access height 100 mm.

Colour:

Reseda green RAL 6011.
 Height: 610 mm
 Width: 820 mm
 Depth: 710 mm
 Drive-in width: 290 mm
 Drive-in depth: 720 mm
 Safe working load: 800 kg

Technical description

Height	610 mm
Stacking edge on 3 sides	yes
Pass-under height	100 mm
Weight	35 kg
mixed stacking of different sizes is possible.	yes

Safe working load	800 kg
Material	Sheet steel
Wall version	with component removal opening
Drive-in depth	720 mm
Depth	710 mm
can be lifted by crane	no
Colour	reseda green RAL 6011
Width	820 mm
with fork insertion slots	no
Drive-in width	290 mm
Stackable load	2400 kg
Attachment brackets with lifting eyes	no
stackable	yes
Nominal width	800 mm
Nominal depth	700 mm
Manufacturer's designation	Lager-Fix storage container
Type of product	Transport and stacking large container