



## Stackable box with removal opening, Nominal size depth×width: 1000X500 mm



### Order data

Order number	963529 1000X500
GTIN	4052939488233
Item class	96l

### Description

#### Version:

Made of sheet metal. High load capacity due to pressed steel sides with corner inserts. Reinforced feet. Stacking edge round three sides (stackable up to 6 units). Access height 100 mm. Stacking edge round three sides (stackable up to 6 units). Access height 100 mm.

#### Colour:

Reseda green RAL 6011.  
 Height: 610 mm  
 Width: 520 mm  
 Depth: 1010 mm  
 Drive-in width: 600 mm  
 Drive-in depth: 420 mm  
 Safe working load: 800 kg

### Technical description

Colour	reseda green RAL 6011
Height	610 mm
Stacking edge on 3 sides	yes
Drive-in depth	420 mm
Pass-under height	100 mm

Safe working load	800 kg
Material	Sheet steel
Stackable load	3200 kg
stackable	yes
mixed stacking of different sizes is possible.	yes
Weight	36 kg
Depth	1010 mm
Drive-in width	600 mm
with fork insertion slots	no
Attachment brackets with lifting eyes	no
Width	520 mm
Wall version	with component removal opening
can be lifted by crane	no
Nominal width	500 mm
Nominal depth	1000 mm
Type of product	Transport and stacking large container