



Stackable box with removal opening, Nominal size depth×width: 1200X800 mm



Order data

| | |
|--------------|-----------------|
| Order number | 963529 1200X800 |
| GTIN | 4052939488240 |
| Item class | 96l |

Description

Version:

Made of sheet metal. High load capacity due to pressed steel sides with corner inserts. Reinforced feet. Stacking edge round three sides (stackable up to 6 units). Access height 100 mm. Stacking edge round three sides (stackable up to 6 units). Access height 100 mm.

Colour:

Reseda green RAL 6011.
 Height: 610 mm
 Width: 820 mm
 Depth: 1210 mm
 Drive-in width: 800 mm
 Drive-in depth: 720 mm
 Safe working load: 1000 kg

Technical description

| | |
|---------------------------------------|--------------------------------|
| Wall version | with component removal opening |
| Depth | 1210 mm |
| stackable | yes |
| Colour | reseda green RAL 6011 |
| Attachment brackets with lifting eyes | no |

| | |
|--|---|
| Weight | 55 kg |
| with fork insertion slots | no |
| can be lifted by crane | no |
| Material | Sheet steel |
| Width | 820 mm |
| Drive-in width | 800 mm |
| Pass-under height | 100 mm |
| Stackable load | 5000 kg |
| Drive-in depth | 720 mm |
| Stacking edge on 3 sides | yes |
| Height | 610 mm |
| mixed stacking of different sizes is possible. | yes |
| Safe working load | 1000 kg |
| Nominal width | 800 mm |
| Nominal depth | 1200 mm |
| Type of product | Transport and stacking large container |