



## Containment tray for 1000 litre IBC with galvanised grid, Number of IBC×IBC Contents (l): 2X1000



### Order data

Order number	981460 2X1000
GTIN	4250101100734
Item class	96V

### Description

#### Version:

Of polyethylene (PE) – light, weatherproof, robust.

#### Application:

For secure storage of containers **IBC** (Intermediate Bulk Containers) and **CTC** (Cubic Tank Containers). **For storage of water-polluting liquids of GHS categories 1 – 4.** Especially **resistant to acids, alkalis** and oils. Depending on the tare weight of the IBC/CTC, suitable for liquids with a maximum specific weight of 1800 kg/m<sup>3</sup>.

**Storage of flammable media is not permitted** (applies to Germany).

#### Standard:

Allgemeine Bauaufsichtliche Zulassung des DIBt, Berlin und Übereinstimmungserklärung (ÜHP).

Storage: Storage of corrosive substances permitted

Drip catch volume: 1000 l

Height: 580 mm

Width: 2530 mm

Depth: 1320 mm

Safe working load: 4000 kg

### Technical description

Drip catch volume	1000 l
-------------------	--------

Safe working load	4000 kg
Height	580 mm
Width	2530 mm
IBC contents	1000 l
Depth	1320 mm
Storage	Storage of environmentally polluting substances
Storage	Storage of water polluting substances class 1-3
Storage	Storage of flammable substances prohibited
Storage	Storage of corrosive substances permitted
Type of product	Drip tray