

**Pair of gloves 6705, Glove size: 8****Order data**

Order number	094530 8
GTIN	4059904096615
Item class	09H

**Description****Version:**

6705. PU coating for high breathability and freedom of movement for working in damp but not oily environments.

**Version of the advertising text:**

Cut-resistant gloves (class 5) with **outstanding cost-benefit ratio**.

**Standard:**

EN 388; EN ISO 21420

**Note:**

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

**Technical description**

EN 388 abrasion resistance	4
EN 388 penetration resistance	2
Breathability	good
Wet grip	medium

DMF-free	no
EN 388 cut resistance	5
Material of coating	PU
Oil grip	medium
EN 388 tear propagation resistance	4
Glove size	8
Heat protection	good
Touch sensitivity	good
silicone-free	yes
Accuracy of fit	good
Type of glove	Multi-purpose gloves
Protection category	Category II
Contents	10
Knitted technology	13G
EN 388	4442C
EN 407	X1XXXX
Backing material	Taeki
Coating	PU
Coating variant	The palms of the hands
Application range	All-round
Colour	black / grey
Standard	EN 407
Weight	31.8 g
Application	reusable
Cut protection class	C
Type of product	Cut-resistant gloves