

Wide-span basic rack, Depth 621 mm, Height / Shelf width: 1981/2450mm**Order data**

| | |
|--------------|------------------|
| Order number | 990865 1981/2450 |
| GTIN | 4004514224613 |
| Item class | 96P |

Description**Version:**

With 16 mm chipboard shelves. Storage shelves adjustable at 38-mm intervals. Quick assembly without screws, using keyholes in the profiles. Maximum **shelf loading**: up to 720 kg, maximum **bay load capacity**: up to 3200 kg.

Description:**Assembled size:**

Basic rack: Nominal size = Overall size in mm

Overall depth of the rack: Nominal size = Overall size in mm

Application:

Storage of awkward and bulky goods. Deposit and retrieval available from both sides. Particularly easy handling and assembly.

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **Available only as a base rack, not as an add-on rack. If required, 2 or more base racks can be fastened together using connectors (included in delivery) to form a row of racks.**
- **The free unsupported length (K) must not be more than 100 mm. The permissible bay load must be reduced in recognition of this shelf.**
- **Floor and wall fastenings are not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|------------------------------------------|-------------------|
| Number of storage levels chipboard shelf | 4 |
| Height | 1981 mm |
| Storage shelf depth | 621 mm |
| Width | 2450 mm |
| Shelf load capacity | 545 kg |
| Rack installation | Basic rack |
| Bay width = assembled size | 2450 mm |
| Customer assembly | yes |
| Shelf width | 2450 mm |
| Material of storage level | Chipboard shelf |
| Depth | 621 mm |
| Rack depth | 621 mm |
| Rack width | 2450 mm |
| Rack height | 1981 mm |
| Insert thickness | 16 mm |
| Height adjustment interval | 38 mm |
| Type of installation | Plug-in racking |
| Colour selection | RAL 5010, 2004 |
| Product name attribute | Depth 621 mm |
| Type of product | Wide-span racking |