

## PRYOR

Steel type punches individually exchangeable, for set No. 085480, Character height / Characters: 2/&mm



### Order data

Order number	085481 2/&
GTIN	5022044024762
Item class	08W

### Description

#### Version:

Size 1.5/\* to size 5/\* = number (0 - 9), letter (A - Z) and special characters (&, /, +, -, full stop, comma).

Size 1.5LEER to size 5LEER – spacer piece.

#### Note:

**The asterisk in the stated size acts as a placeholder for the required characters.**

When ordering please state the size (e.g. 3/\*) to be extended with the desired character, e.g. 3/1, 3/A or 3/& etc.

Width of punch type: 2 mm

Punch type depth: 19.05 mm

Height of punch type: 6.35 mm

### Technical description

Character	AND symbol
Width of punch type	2 mm
Character height	2 mm

Punch type depth	19.05 mm
Height of punch type	6.35 mm
Type of product	Hand punch