

Wide-span basic rack, Depth 621 mm, Height / Shelf width: 2438/1536mm**Order data**

Order number	990865 2438/1536
GTIN	4004514224651
Item class	96P

Description**Version:**

With 16 mm chipboard shelves. Storage shelves adjustable at 38-mm intervals. Quick assembly without screws, using keyholes in the profiles. Maximum **shelf loading**: up to 720 kg, maximum **bay load capacity**: up to 3200 kg.

Description:**Assembled size:**

Basic rack: Nominal size = Overall size in mm

Overall depth of the rack: Nominal size = Overall size in mm

Application:

Storage of awkward and bulky goods. Deposit and retrieval available from both sides. Particularly easy handling and assembly.

Colour:

Stiles similar RAL 5017 Traffic blue, cross beams similar to RAL 2004 Pure orange **powder-coated**.

Note:

- **Available only as a base rack, not as an add-on rack. If required, 2 or more base racks can be fastened together using connectors (included in delivery) to form a row of racks.**
- **The free unsupported length (K) must not be more than 100 mm. The permissible bay load must be reduced in recognition of this shelf.**
- **Floor and wall fastenings are not included.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

Rack installation	Basic rack
Customer assembly	yes
Width	1536 mm
Material of storage level	Chipboard shelf
Shelf width	1536 mm
Bay width = assembled size	1536 mm
Shelf load capacity	640 kg
Number of storage levels chipboard shelf	4
Storage shelf depth	621 mm
Height	2438 mm
Depth	621 mm
Rack depth	621 mm
Rack width	1536 mm
Rack height	2438 mm
Insert thickness	16 mm
Height adjustment interval	38 mm
Type of installation	Plug-in racking
Colour selection	RAL 5010, 2004
Product name attribute	Depth 621 mm
Type of product	Wide-span racking