

Workplace mat Top Width 91 cm, black, Length: 200cm



Order data

Order number	964528 200
GTIN	662641658011
Item class	96C

Description

Version:

These industrial workplace mats are made of high quality plastic for **heavy-duty use**:

- **Hard and wear-resistant vinyl surface for optimum slip-resistance and long service life.**
- **Soft vinyl foam core for anti-fatiguing characteristics. Laminated to the vinyl surface.**
- **Non-slip underside RedStop™.**
- **Bevelled edges on all sides to eliminate the risk of tripping when walking on to the mat.**
- **Limited resistance to most industrial greases, media and chemicals. Unsuitable for cooling lubricants.**
- **Sealed all round to prevent penetration of moisture.**
- **Fire resistant to DIN 4102 B1.**
- **Mat thickness: 14.3 mm, weight: approx. 6.5 kg/m².**
- **Non-slip characteristics R10 to DIN 51130 and BGR 181.**

Technical description

Weight	12 kg
Bevelling	4-sided
plug-in	no

Non-slip underside	yes
Material	Vinyl foam core
Width	91 cm
Surface	Vinyl
with safety edges	2-sided
Length	200 cm
Thickness	14.3 mm
resistant to a limited extent against most	industrial greases, solvents, chemicals
Weight per unit area	6.5 kg/m ²
Non-slip characteristics to DIN 51130, BGR 181	R10
Standing in comfort	Anti-slip
Standing in comfort	Insulation (temperature)
Standing in comfort	Anti-fatiguing
Shock protection	Floor
Material characteristics	not oil-resistant
Colour	black
Type of product	Workplace mat