

Nitrile rubber floor mat, sealed surface, with safety edges, black / orange, width×length: 97X163cm



Order data

Order number	964621 97X163
GTIN	662641855625
Item class	96C

Description

Version:

Industrial nitrile rubber floor mat with easily visible **orange-coloured safety edges** on three sides.

- **Additional bars on the underside provide generous "storage space" for dirt and liquids - the surface remains clean, dry and non-slip.**
- **Long life robust nitrile rubber with high wear resistance.**
- **Highly non-slip surface and secure positioning on the floor, even when wet. Mat thickness: 22 mm, weight: approx. 13 kg/m².**
- **Resistant to industrial oils and most chemicals.**
- **Non-slip characteristics tested to DIN 51130 and BGR 181.**

Nitrile rubber floor mat with sealed surface.

Note:

Special sizes available on request on a module of 30.5×30.5 cm plus 5 cm edge strip all round.

Technical description

Length	163 cm
--------	--------

with safety edges	3-sided
Material	Nitrile rubber
Weight per unit area	13 kg/m ²
Width	97 cm
Thickness	22 mm
plug-in	no
Manufacturer's designation	Safety Stance Solid™ Nitrile
Standing in comfort	Insulation (temperature)
Standing in comfort	Anti-slip
Standing in comfort	Anti-fatiguing
Shock protection	Floor
Material characteristics	oil-resistant
Colour	black / orange
Type of product	Workplace mat