

## Racking tray painted, with grid, suitable for cross beam length (mm) / Drip catch volume (l): 1800/240



### Order data

Order number	983015 1800/240
GTIN	2050001937667
Item class	96U

### Description

**Version:**

Made of 3 mm sheet metal. Access height 100 mm.  
With galvanised grid.

**Application:**

For safe storage and discharging of drums. For **flammable liquids of GHS categories 1 – 3** and for **water-polluting liquids of GHS categories 1 – 4**.

**Standard:**

Übereinstimmungserklärung (ÜHP) gemäß Bauregelliste nach Richtlinie der StawaR (Stahlwannenrichtlinie).

**Suitable for:**

Pallet racking of depth 1100 mm.

**Colour:**

**Standard paint finish light blue RAL 5012.**

### Technical description

Height	250 mm
Drip catch volume	240 l
Weight	134 kg
Depth	1300 mm
suitable for cross beam length	1800 mm
Width	1750 mm

Floor loading	1000 kg/m <sup>2</sup>
Material thickness	3 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Storage	Storage of flammable substances permitted
Storage	Storage of corrosive substances prohibited
Storage	Storage of environmentally polluting substances
Storage	Storage of water polluting substances class 1-3
Type of product	Racking tray