

Racking tray galvanised, with grid, suitable for cross beam length (mm) / Drip catch volume (l): 1800/240



Order data

Order number	983005 1800/240
GTIN	4052462030770
Item class	96U

Description

Version:

Made of 3 mm sheet metal. Access height 100 mm.

Hot-dip galvanised to EN ISO 1461.

With galvanised grid.

Application:

For safe storage and discharging of drums. For **flammable liquids of GHS categories 1 – 3** and for **water-polluting liquids of GHS categories 1 – 4**.

Standard:

Übereinstimmungserklärung (ÜHP) gemäß Bauregelliste nach Richtlinie der StawaR (Stahlwannenrichtlinie).

Suitable for:

Pallet racking of depth 1100 mm.

Technical description

suitable for cross beam length	1800 mm
Height	250 mm
Depth	1300 mm
Drip catch volume	240 l
Width	1750 mm
Weight	141 kg
Floor loading	1000 kg/m ²

Material thickness	3 mm
Material	galvanised
Storage	Storage of flammable substances permitted
Storage	Storage of corrosive substances prohibited
Storage	Storage of environmentally polluting substances
Storage	Storage of water polluting substances class 1-3
Type of product	Racking tray