

Slot-in tray painted, with grid, suitable for cross beam length (mm) / Drip catch volume (l): 2700/200



Order data

Order number	983045 2700/200
GTIN	2050001937698
Item class	96U

Description

Version:

Made of 3 mm sheet metal. Access height 100 mm.
With galvanised grid.

Application:

For safe storage and discharging of drums. For **flammable liquids of GHS categories 1 – 3** and for **water-polluting liquids of GHS categories 1 – 4**.

Standard:

Übereinstimmungserklärung (ÜHP) gemäß Bauregelliste nach Richtlinie der StawaR (Stahlwannenrichtlinie).

Suitable for:

Pallet racking of depth 1100 mm. Suitable for insertion in pallet racking No. 991202 – 991227.

Colour:

Standard paint finish light blue RAL 5012.

Technical description

suitable for cross beam length	2700 mm
Drip catch volume	200 l
Depth	1250 mm
Internal depth	915 mm
Weight	151 kg
Width	2650 mm

Height	130 mm
Floor loading	1000 kg/m ²
Material thickness	3 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Storage	Storage of environmentally polluting substances
Storage	Storage of corrosive substances prohibited
Storage	Storage of flammable substances permitted
Storage	Storage of water polluting substances class 1-3
Type of product	Racking tray