

Garant

eco grooving tool strengthened, left-hand, Blade height h₅ / groove width w: 26/3Lmm

**Order data**

Order number	273855 26/3L
GTIN	4045197989185
Item class	21W

Description**Version:**

With eco cooling directly to the cutting edge and additional rake face cooling.
With coolant transfer for toolholders from other manufacturers.

Attention:

Please order the assembly key No. 279920 separately.

Note:

Due to its design, it is not compatible with EWS toolholders No. 319148 and 319149.
Please order the assembly key No. 279920 separately. From 19.5 mm groove depth onwards the second cutter comes into contact with the workpiece. This can lead to scoring. If necessary, use single-ended grooving inserts No. 273656 – 273670.

Technical description

Height h ₁	21.4 mm
for maximum workpiece Ø	90 mm
Series	Eco
Blade height h ₅	26 mm
Overall length L	96 mm
Application type	left-hand
Through-coolant	yes
axial grooving possible	no

Type of product

Parting-off tool